

END EFFECTORS

Electric Gripper





Features

- Integrated with stepper motor and encoder featuring status feedback, abnormal alarm, object identification and signal output.
- Using linear module to achieve high speed, high precision, high rigidity, high efficiency and advantage of compact size.
- Equipped with auto-reset and gripping force adjustment for smart function like real-time adaptive capture.
- Direction, stroke, force, speed etc. can be set, and the software has the function of using the recorded history.
- Supports both serial and I/O communications, providing flexibility and convenience to users.

Model		XEG-32	
Total Stroke (mm)		32	
Gripping	Force (N)	60~150	
Speed	Moving	1~80	
(mm/s)	Gripping	1~20	
Repeatab	ility (mm)	±0.01	
Weigh	nt (kg)	0.7	
IP C	lass	IP20	
Cleanroom Class		ISO Class 5 (Class 100)	

* Note 1: The weight of workpiece[kg] accelaration of gravity 9.81(m/s²) should be 1/10~1/20 of the gripping force(N).If the gripper holding a workpiece moves or turns with high-acceleration/deceleration, choose the model with higher force allowance.

* Note 2: To find out more details for the projects of "TM Robotics Plug & Play" and "UR+ Robotics Solutions", please visit HIWIN official website.

Electric Gripper





Features

- Integrated with stepper motor and encoder featuring status feedback, abnormal alarm, object identification and signal output.
- Using linear module to achieve high speed, high precision, high rigidity, high efficiency and advantage of compact size.
- Equipped with auto-reset and gripping force adjustment for smart function like real-time adaptive capture.
- Direction, stroke, force, speed etc. can be set, and the software has the function of using the recorded history.
- Supports both serial and I/O communications, providing flexibility and convenience to users.

Model		XEG-64	
Total Stroke (mm)		64	
Gripping Force (N)		180~450	
Speed	Moving	1~100	
(mm/s)	Gripping	1~20	
Repeatability (mm)		±0.01	
Weight (kg)		1.9	
IP Class		IP20	
Cleanroom Class		ISO Class 5 (Class 100)	

* Note 1: The weight of workpiece[kg] accelaration of gravity 9.81(m/s²) should be 1/10~1/20 of the gripping force[N]. If the gripper holding a workpiece moves or turns with high-acceleration/deceleration, choose the model with higher force allowance.

* Note 2: To find out more details for the projects of "TM Robotics Plug & Play" and "UR+ Robotics Solutions", please visit HIWIN official website.

Electric Gripper Controller	Model		XEG-C1
	Voltage (V)		DC24±10%
XEG Series	Current (A)		0.5
AEG Series	External I/0	Input	5 points: Command point setting 1 point: Command input
		Output	6 point: motion output
	Serial Communication		RS232(USB)
	Number of Points	External I/0	30+1 set (Include original reset)
		Serial Communication	Unlimited
HIWIN.xEG.CI	IP		20
	Weight (kg)		0.15
	Safety Circuit		N/A
and the second s	ID Setting		N/A
XEG-C1	Terminal Resistor		N/A
	Model		
	1	Model	XEG-C2
			XEG-C2
GOOD DESIGN RETAIWAN CE ROHS	Vol	Model tage (V) Trent (A)	
GOOD DESIGN RECEILENCE 2017 CE ROBES	Vol	tage (V)	DC24±10%
and a	Vol	tage (V) -rent (A)	DC24±10% 0.5 6 points: Command point setting 1 point: Command input
##	Vol Cur External I/O	tage (V) rrent (A) Input	DC24±10% 0.5 6 points: Command point setting 1 point: Command input 1 point: Firmware version update
##	Vol Cur External I/O Serial Co	tage (V) rrent (A) Input Output	DC24±10% 0.5 6 points: Command point setting 1 point: Command input 1 point: Firmware version update 8 point: motion output
	Vol Cur External I/O	tage (V) rrent (A) Input Output ommunication	DC24±10% 0.5 6 points: Command point setting 1 point: Command input 1 point: Firmware version update 8 point: motion output RS485[Modbus-RTU]
	Vol Cur External I/O Serial Co	tage (V) rrent (A) Input Output ommunication External I/O	DC24±10% 0.5 6 points: Command point setting 1 point: Command input 1 point: Firmware version update 8 point: motion output RS485(Modbus-RTU) 62+1 set (Include original reset)
	Vol Cur External I/O Serial Co Number of Points	tage (V) rrent (A) Input Output ommunication External I/O Serial Communication	DC24±10% 0.5 6 points: Command point setting 1 point: Command input 1 point: Firmware version update 8 point: motion output RS485(Modbus-RTU) 62+1 set (Include original reset) Unlimited
	Vol Cur External I/O Serial Co Number of Points We	tage (V) rrent (A) Input Output ommunication External I/O Serial Communication IP	DC24±10% 0.5 6 points: Command point setting 1 point: Command input 1 point: Firmware version update 8 point: motion output RS485(Modbus-RTU) 62+1 set (Include original reset) Unlimited 20
	Vol Cur External I/O Serial Co Number of Points We Safe	tage (V) rrent (A) Input Output ommunication External I/O Serial Communication IP ight (kg)	DC24±10% 0.5 6 points: Command point setting 1 point: Command input 1 point: Firmware version update 8 point: motion output RS485(Modbus-RTU) 62+1 set (Include original reset) Unlimited 20 0.3 Trigger emergency stop

Integrated Electric Gripper SEG Series





SEG-24

Features

- Integrated control system The controller is embedded inside the gripper and the system has built-in motion parameters.
- User friendly Users control I / O signals easily, no need to edit programs and parameters.
- SEG-24

Press to set up high-efficiency grip mode on gripper panel, with instant adaptive grip, mode adjustment and other intelligent function.

Model			SEG-24
	Stroke Per Side (mm)		12
Gripper Spec.	Gripping Force (N)		35
	Speed (mm/s)	Moving	45
		Gripping	15
	Repeatability (mm)		±0.1
	Weight (kg)		0.7
	Voltage (V)		24
	Current (A)		0.5
	IP		20

* Note 1: The weight of workpiece[kg] accelaration of gravity 9.81(m/s²) should be 1/10~1/20 of the gripping force[N]. If the gripper holding a workpiece moves or turns with high-acceleration/deceleration, choose the model with higher force allowance.

* Note 2: To find out more details for the projects of "TM Robotics Plug & Play" and "UR+ Robotics Solutions", please visit HIWIN official website.

Global Sales and Customer Service Site

HIWIN GmbH OFFENBURG, GERMANY www.hiwin.de www.hiwin.eu info@hiwin.de

HIWIN JAPAN KOBE • NAGOYA • TOKYO • NAGANO • TOHOKU • SHIZUOKA • HOKURIKU • HIROSHIMA • FUKUOKA • KUMAMOTO, JAPAN www.hiwin.co.jp info@hiwin.co.ip

HIWIN USA CHICAGO, U.S.A. www.hiwin.us info@hiwin.com

HIWIN Srl BRUGHERIO, ITALY www.hiwin.it info@hiwin.it

from unknown sources.

various factors including product improvements.

HIWIN Schweiz GmbH JONA. SWITZERLAND www.hiwin.ch info@hiwin.ch

BRNO, CZECH REPUBLIC info@hiwin.cz

HIWIN FRANCE STRASBOURG, FRANCE www.hiwin.fr info@hiwin.de

HIWIN SINGAPORE

SINGAPORE www.hiwin.sg info@hiwin.sg HIWIN KORFA SUWON • CHANGWON, KOREA www.hiwin.kr info@hiwin.kr

HIWIN CHINA SUZHOU, CHINA www.hiwin.cn info@hiwin.cn

Mega-Fabs Motion Systems,

Ltd. HAIFA, ISRAEL www.mega-fabs.com info@mega-fabs.com

> The specifications in this catalog are subject to change without notification.

• HIWIN website for patented product directory: http://www.hiwin.tw/Products/Products_patents.aspx • HIWIN will not sell or export products or processes restricted under the "Foreign Trade Act" or related regulations. Export of restricted products should be approved by proper authorities in accordance with relevant laws and shall not be used to manufacture or develop nuclear, biochemical, missiles or other weapons.

• Actual products may differ from specifications and photos provided in this catalog. These differences may be the result of

HIWIN is a registered trademark of HIWIN Technologies Corp., For your protection, avoid buying counterfeit products

Copyright © HIWIN Technologies Corp. ©2023 FORM C98DE05-2304 (PRINTED IN TAIWAN)

HIWIN_®

HIWIN TECHNOLOGIES CORP. No. 7, Jingke Road, Taichung Precision Machinery Park, Taichung 40852, Taiwan Tel: +886-4-23594510 Fax: +886-4-23594420 www.hiwin.tw www.hiwinsupport.com business@hiwin.tw

HIWIN s.r.o. www.hiwin.cz